






Printed copy for information only/
Ausdruck nur zur Information

- Specification:

 - Performance requirements at equilibrium condition standard atmosphere 23 °C / 50% RH
 - Material: PA6.6
 - Bundle Ø/ Tensile force/
- Spezifikation:

 - Leistungsanforderung im Gleichgewichtszustand Normalklima 23 °C / 50% RH
 - Material: PA6.6
 - Buendel Ø: 1-35 mm
 - Schlaufenhaltekraft: min. 180 N

The manufacturing-related geometry changes (injection point, ejectors marks, etc.) allowed. Design of the details are left to suppliers discretion.

Durch das Herstellverfahren bedingte Geometriaeänderungen (Anspritzung, Auswerfermarkierungen, etc.) zulaessig. Einzelheiten der Ausfuehrung bleiben dem Hersteller ueberlassen.

Revision Level			Revision Record			The copyright of this drawing is reserved by HellermannTyton.	Drawn		Date (YYYY/MM/DD)	Title	T50SOSEC34E	Scale 1:1						
Drawing	State	Part	Material specification changed				I.Langeloh	2006/05/02										
03.2	Design Release	3					Approved	Date (YYYY/MM/DD)										
Changed	Date (YYYY/MM/DD)						B.Schiwek	2006/05/02										
A.Hiller	2020/03/12					All drawing revisions are stored in CAD PDM database	Units	 HellermannTyton www.HellermannTyton.com		Drawing-No 14.1963	Global Project Number NT 049-05							
Approved	Date (YYYY/MM/DD)						mm				Format A2							
B.Schiwek	2020/03/12																	
										Sheet 1 / 1								