



Metallic conduits with liquid-tight cover

- LTS Galvanised Steel Conduit, PVC Cover

Machine tools or outdoor installations, wherever liquid-tight (IP68) is a requirement.

Features and Benefits

- Liquid-tight (IP68 and IP69k with LTS fittings)
- High compression, tensile and impact strength
- Good flexibility
- Smooth outer cover does not wrinkle when bent
- Good resistance to acids, petrol, oils and greases
- UV-resistant, suitable for outdoor use
- Colour: black




HelaGuard LTS.

Liquid-tight conduits with polyurethane (PU) cover also available.

MATERIAL	Galvanised Steel (GS), Polyvinylchloride (PVC)
Operating Temperature	-20 °C to +105 °C
Specifications	Lloyd's Register

RoHS ✓



HelaGuard liquid-tight metallic conduit, plastic coating



HelaGuard LTS galvanised steel conduit with a smooth, liquid-tight PVC cover is ideal for outdoor installations.

TYPE	Nominal Ø	US Trade Size	Outside Ø (OD)	Inside Ø (ID)	Min. Bending Radius (R)	Weight (g/m)	Reel Length	Colour	Article-No.
LTS10	10	1/4 "	11.8	7.0	35	185	50 m	Black (BK)	166-31900
LTS12	12	5/16 "	14.2	10.0	40	203	25 m	Black (BK)	166-31901
LTS16	16	3/8 "	17.8	12.6	45	311	25 m	Black (BK)	166-31902
	16	3/8 "	17.8	12.6	45	311	25 m	Grey (GY)	166-31917
LTS20	20	1/2 "	21.1	16.0	65	407	25 m	Black (BK)	166-31903
	20	1/2 "	21.1	16.0	65	407	25 m	Grey (GY)	166-31918
LTS25	25	3/4 "	26.4	21.1	100	503	25 m	Black (BK)	166-31904
	25	3/4 "	26.4	21.1	100	503	25 m	Grey (GY)	166-31919
LTS32	32	1 "	33.1	26.5	135	732	25 m	Black (BK)	166-31905
	32	1 "	33.1	26.5	135	732	25 m	Grey (GY)	166-31921
LTS40	40	1 1/4 "	41.8	35.4	175	885	25 m	Black (BK)	166-31906
	40	1 1/4 "	41.8	35.4	175	885	25 m	Grey (GY)	166-31927
LTS50	50	1 1/2 "	47.9	40.4	230	1,240	25 m	Black (BK)	166-31907
LTS63	63	2 "	59.7	51.6	280	1,470	10 m	Black (BK)	166-31908

All dimensions in mm. Subject to technical changes. Other reel lengths available on request. Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval.