



Heat Shrinkable Tubing 4:1 - Flame retardant

HA40 - thick wall adhesive lined

Designed for low voltage cable joints and terminations in shipbuilding. Insulates and protects against moisture.

Features and Benefits

- Thick walled adhesive lined shrink tubing for low voltage power cables
- Designed for shipbuilding, Germanische Lloyd approved
- Flame retarded
- UV and weather resistant
- Excellent mechanical performance



HA40 thick wall, adhesive lined and flame retarded tubing for shipbuilding applications.




Detailed Information about Heatguns please refer to page 529.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	4:1
Operating Temperature	-55 °C to +110 °C
Minimum Shrink Temperature	+120 °C
Softening Point Adhesive	+85 °C
Longitudinal change after shrinkage	-10 % max.
Dielectric Strength	>18 kV/mm
Flammability	Self extinguishing
Specifications	GL

LFH ✓

RoHS ✓



Heat Shrinkable Tubing 4:1 with adhesive

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Article-No.
HA40 9/3	9.0	3.0	1.80	1.0 m	Black (BK)	321-00100
HA40 13/4	13.0	4.0	2.20	1.0 m	Black (BK)	321-00101
HA40 22/6	22.0	6.0	2.70	1.0 m	Black (BK)	321-00102
HA40 33/8	33.0	8.0	2.70	1.0 m	Black (BK)	321-00103
HA40 40/12	40.0	12.0	4.00	1.0 m	Black (BK)	321-00104
HA40 55/16	55.0	16.0	4.00	1.0 m	Black (BK)	321-00105
HA40 75/22	75.0	22.0	4.10	1.0 m	Black (BK)	321-00106
HA40 92/25	92.0	25.0	4.20	1.0 m	Black (BK)	321-00107

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.