

LOCK SWITCH



WRL IP66/IP67 SEALED LOCK SWITCH

ELECTRICAL & MECHANICAL SPECIFICATION

Switch Rating: 1A @24V ac/dc Life: >10,000 Cycles

Proof Voltage: 750 Vac (Initial) Lock Type: 5 Disc

Insulation Resistance: >999MΩ @ 500Vdc (Initial) Operating Temperature: -20°C to +65°C

 ${\color{red} \textbf{Contact Resistance:}} \qquad {\color{red} <20m\Omega \, (Initial)} \qquad {\color{red} \textbf{Lock Housing:}} \qquad {\color{red} Zinc \, Alloy \, Bright \, Cr \, Plated}$

Contact Material: Brass CZ108, Ag Plated **Moulding Material**: Polyamide 6.6 G.F. VO Rated

FEATURES


Suitable for Marine Environment Exposure to Severity One (EN60068-2-52) salt mist tested

Front assembly
Single or Double pole
Max panel thickness 3.5mm
Rear panel depth - <30mm
Made in UK

2 keys per switch Up to 200 differ key combinations available Keys are double entry (can be inserted into lock either way up) Moulded bezel available for parallel lock headed version (SRL02101). Oil regularly if used outside



SINGLE POLE LOCK SWITCH






TAPERED LOCK HEAD 90° INDEXING

BASIC PART No.	TOTAL MOVEMENT	INDEXING	KEY WITHDRAWAL POSITIONS	SWITCH CONFIGURATION
WRL-5-D	90°	90°	1,4	12
WRL-5-E	90°	90°	1 ONLY	
WRL-5-F WRL-5-V WRL-5-W	180° 180° 180°	90° 90° 90°	1,4,7 1,4 1 ONLY	1 OFF 2 3
WRL-5-P	180°	90°	1,4,7	1
WRL-5-T	180°	90°	1,4,7	1 OFF
WRL-5-Q	180°	90°	4 ONLY	3 OFF 4

DOUBLE POLE LOCK SWITCH



TAPERED LOCK HEAD 60° INDEXING

BASIC PART No.	TOTAL MOVEMENT	INDEXING	KEY WITHDRAWAL POSITIONS	SWITCH CONFIGURATION
WRL-3-L	609	6D°	1,3	
WRL-5-M	60°	6D°	1 ONLY	=

WRL ORDERING CODE

