

LOCTITE ABLESTIK QMI519LB

November 2016

PRODUCT DESCRIPTION

LOCTITE ABLESTIK QMI519LB provides the following product characteristics:

Technology	BMI/Acrylate
Appearance	Silver
Product Benefits	- Electrically conductive - Thermally conductive - Low resin bleed - One component - Ease of use - Void-free bondline - Hydrophobic - Stable at high temperatures - High resistance to delamination - Good resistance to "popcorning" after exposure to reflow temperatures
Cure	Heat cure
Application	Die attach
Key Substrates	Wide variety of metals and ceramic surfaces, Copper, Silver, Palladium and Alloy 42
Typical Package Application	SOIC, SOP, QFP and QFN type packages

LOCTITE ABLESTIK QMI519LB silver filled conductive adhesive is recommended for use in bonding integrated circuits and components to metal leadframes. It is designed to achieve UPHs several orders of magnitude higher than conventional oven cured adhesives. Maximum productivity is realized through in-line cure, either on the diebonder using a post diebond heater or on the wirebonder preheater. Studies have also shown improved coplanarity in parts cured on the diebonder.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):

Speed 5 rpm 15,000

Thixotropic Index (Speed 0.5/speed 5) 5.02

Specific Gravity @ 25 °C 4.0

Work Life by viscosity, hours 48

Shelf Life @ -40°C (from date of manufacture), days 365

Flash Point - See SDS

TYPICAL CURING PERFORMANCE

SkipCure Process

≥10 seconds @ 200°C

Alternative Cure Schedule 1

15minutes @ 185°C (maybe suitable for QFN packages)

Alternative Cure Schedule 2

15minutes @ 200 to 220°C (for higher adhesion)

The above cure profile is a guideline recommendation. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion :

Below Tg, ppm/°C 40

Above Tg, ppm/°C 140

Glass Transition Temperature, TMA, °C 150

Dynamic Tensile Modulus N/mm² (psi) 6,000 (870,226)

Extractable Ionic Content, , ppm:

Chloride (Cl-) <20

Sodium (Na+) <20

Potassium (K+) <20

Electrical Properties

Volume Resistivity, ohm-cm 0.0001

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous

Die Shear Strength :

2 x 2 mm Si die @ 25°C, kg-f:

on Au LF 15

on PPF LF 10

2 x 2 mm Si die @ 25 °C, kg-f:

After PMC (4 hours @ 175°C) 3.3

After PB (16 hours @ 121°C) 2.7

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

THAWING:

1. Allow material to reach room temperature before use.
2. After removing from the freezer, set the syringes to stand vertically while thawing.
3. DO NOT open the container before contents reach 25°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
4. DO NOT re-freeze. Once thawed to -40°C, the adhesive should not be re-frozen..

DIRECTIONS FOR USE

1. Thawed adhesive should immediately be placed on dispense equipment for use.
2. If the adhesive is transferred to a final dispensing reservoir, care must be exercised to avoid entrapment of contaminants and/or air into the adhesive.

3. Adhesive must be completely used within the product's recommended work life.
4. Silver-resin separation may occur if the adhesive is left out at room temperature, beyond the recommended work life.
5. Apply enough adhesive to achieve a 25 to 50 µm wet bondline thickness, dispensed with approximately 25 to 50 % filleting on all sides of the die.
6. Alternate dispense amounts may be used depending on the application requirements..
7. Star or crossed shaped dispense patterns will yield fewer bondline voids than the matrix style of dispense pattern.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

STORAGE:

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -40 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada, Inc. the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Reference 0.1