

LOCTITE® ABLESTIK 8175

March 2021

PRODUCT DESCRIPTION

LOCTITE® ABLESTIK 8175 provides the following product characteristics:

Technology	Epoxy
Appearance	Silver
Cure	Heat cure
Product Benefits	- Electrically conductive - Thermally conductive - Stress absorbing - Pb-free alternative to solder - Stencil or screen printable
Application	Die attach

LOCTITE® ABLESTIK 8175 is designed for solder replacement in microelectronic interconnect applications. This adhesive may be used with thick film metallizations or traditional printed circuit board surfaces. It is capable of resolving fine pitch resolution (0.02 inch) when printed using either a stainless steel mesh screen or a metal mask stencil.

MIL-STD-883

LOCTITE® ABLESTIK 8175 meets the requirements of MIL-STD-883, Method 5011.

TYPICAL PROPERTIES OF UNCURED MATERIAL

Thixotropic Index (0.5/5 rpm)	2.0
Viscosity, Brookfield CP51, 25 °C, mPa·s (cP):	
Speed 5 rpm	55,000
Work Life @ 25°C, days	14
Shelf Life @ -40°C, days	365
Flash Point - See SDS	

TYPICAL CURING PERFORMANCE

Cure Schedule

30 minutes @ 150°C

Alternate Cure Schedule

60 minutes @ 150°C (for bondlines <1 mil thick)

Alternative Cure Schedule 2

120 minutes @ 125°C

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Coefficient of Thermal Expansion, ppm/°C:	
Below Tg	55
Above Tg	200
Glass Transition Temperature, °C	90
Thermal Conductivity @ 121°C, W/(m-K)	3.2
Weight Loss @ 300°C, %	0.3
Thermal Shock @ -50 to 150°C, psi	5,000

Electrical Properties

Volume Resistivity, ohms-cm	0.0005
-----------------------------	--------

TYPICAL PERFORMANCE OF CURED MATERIAL

Miscellaneous

Die Shear Strength :	
Cu to Ag metallization @ 25°C, psi	6,200
Lap Shear Strength :	
Al to Al @ 25°C, psi	1,650

GENERAL INFORMATION

Please consult the Safety Data Sheet (SDS) for safe handling information of this product.

THAWING:

1. Allow container to reach room temperature before use.
2. After removing from the freezer, set the syringes to stand vertically while thawing.
3. DO NOT open the container before contents reach 22°C temperature. Any moisture that collects on the thawed container should be removed prior to opening the container.
4. DO NOT re-freeze. Once thawed to 22°C, the adhesive should not be re-frozen.

Surface Preparation

1. Proper preparation of substrates is critical to optimize epoxy adhesive flow and adhesion. The substrate water contact angle (WCA) is a good indicator of the capillary forces that drive resin flow and adhesion. Henkel recommends industry standards of $<50^\circ$ for substrate WCA. This allows the epoxy resin to better wet the substrate. Users may want to establish the precise relationship between WCA and product performance for their specific application.

2. Substrate surface chemistry is impacted by the entire substrate supply chain including supplier manufacturing methods, packaging, handling, plasma treatment, storage conditions, exposure to environment, and subsequent cleaning steps.

Directions for Use

1. Apply adhesive as required.
2. This material may be applied using either a stainless steel mesh screen or a metal mask stencil.
3. The ideal deposition thickness is 0.003 to 0.005 inch.
4. Cure at one of the recommended cure schedules.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage : -40 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local Henkel representative for assistance and recommendations on the specifications of this product.

Conversions

$(^\circ\text{C} \times 1.8) + 32 = ^\circ\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.5