


# TrenchT2™ HiperFET™ Power MOSFET

## IXFH160N15T2


N-Channel Enhancement Mode  
Avalanche Rated  
Fast Intrinsic Diode



$$\begin{aligned} V_{DSS} &= 150V \\ I_{D25} &= 160A \\ R_{DS(on)} &\leq 9.0m\Omega \\ t_{rr} &\leq 160ns \end{aligned}$$

| Symbol     | Test Conditions                                                    | Maximum Ratings |            |
|------------|--------------------------------------------------------------------|-----------------|------------|
| $V_{DSS}$  | $T_J = 25^\circ C$ to $175^\circ C$                                | 150             | V          |
| $V_{DGR}$  | $T_J = 25^\circ C$ to $175^\circ C$ , $R_{GS} = 1M\Omega$          | 150             | V          |
| $V_{GSS}$  | Continuous                                                         | $\pm 20$        | V          |
| $V_{GSM}$  | Transient                                                          | $\pm 30$        | V          |
| $I_{D25}$  | $T_C = 25^\circ C$                                                 | 160             | A          |
| $I_{DM}$   | $T_C = 25^\circ C$ , Pulse Width Limited by $T_{JM}$               | 440             | A          |
| $I_A$      | $T_C = 25^\circ C$                                                 | 80              | A          |
| $E_{AS}$   | $T_C = 25^\circ C$                                                 | 1.5             | J          |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 175^\circ C$ | 15              | V/ns       |
| $P_D$      | $T_C = 25^\circ C$                                                 | 880             | W          |
| $T_J$      |                                                                    | -55 ... +175    | $^\circ C$ |
| $T_{JM}$   |                                                                    | 175             | $^\circ C$ |
| $T_{stg}$  |                                                                    | -55 ... +175    | $^\circ C$ |
| $T_L$      | Maximum Lead Temperature for Soldering                             | 300             | $^\circ C$ |
| $T_{SOLD}$ | Plastic Body for 10s                                               | 260             | $^\circ C$ |
| $M_d$      | Mounting Torque                                                    | 1.13/10         | Nm/lb.in.  |
| Weight     |                                                                    | 6               | g          |

TO-247



G = Gate      D = Drain  
S = Source      Tab = Drain

### Features

- International Standard Package
- High Current Handling Capability
- Fast Intrinsic Diode
- Dynamic  $dv/dt$  Rated
- Avalanche Rated
- Low  $R_{DS(on)}$

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC Motor Drives
- Uninterruptible Power Supplies
- High Speed Power Switching Applications

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |                    |
|--------------|-----------------------------------------------------------------------|-----------------------|------|--------------------|
|              |                                                                       | Min.                  | Typ. | Max.               |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu A$                                      | 150                   |      | V                  |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 1mA$                                       | 2.5                   |      | 4.5 V              |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                    |                       |      | $\pm 200$ nA       |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 150^\circ C$             |                       |      | 10 $\mu A$<br>1 mA |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                   |                       | 7.7  | 9.0 m $\Omega$     |


| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified)                                                                    | Characteristic Values |      |                        |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|------------------------|
|              |                                                                                                                                              | Min.                  | Typ. | Max.                   |
| $g_{fs}$     | $V_{DS} = 10\text{V}, I_D = 60\text{A}$ , Note 1                                                                                             | 80                    | 130  | S                      |
| $C_{iss}$    | $V_{GS} = 0\text{V}, V_{DS} = 25\text{V}, f = 1\text{MHz}$                                                                                   |                       | 15   | nF                     |
| $C_{oss}$    |                                                                                                                                              |                       | 1120 | pF                     |
| $C_{rss}$    |                                                                                                                                              |                       | 113  | pF                     |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$<br>$R_G = 2\Omega$ (External) |                       | 37   | ns                     |
| $t_r$        |                                                                                                                                              |                       | 15   | ns                     |
| $t_{d(off)}$ |                                                                                                                                              |                       | 50   | ns                     |
| $t_f$        |                                                                                                                                              |                       | 26   | ns                     |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$                                                                   |                       | 253  | nC                     |
| $Q_{gs}$     |                                                                                                                                              |                       | 67   | nC                     |
| $Q_{gd}$     |                                                                                                                                              |                       | 73   | nC                     |
| $R_{thJC}$   |                                                                                                                                              |                       |      | $0.17^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                              | 0.21                  |      | $^\circ\text{C/W}$     |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified)                      | Characteristic Values |      |               |
|----------|------------------------------------------------------------------------------------------------|-----------------------|------|---------------|
|          |                                                                                                | Min.                  | Typ. | Max.          |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                           |                       |      | 160 A         |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                    |                       |      | 640 A         |
| $V_{SD}$ | $I_F = 100\text{A}, V_{GS} = 0\text{V}$ , Note 1                                               |                       |      | 1.4 V         |
| $t_{rr}$ | $I_F = 80\text{A}, -di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 75\text{V}, V_{GS} = 0\text{V}$ |                       |      | 160 ns        |
| $I_{RM}$ |                                                                                                |                       | 7.00 | A             |
| $Q_{RM}$ |                                                                                                |                       | 0.32 | $\mu\text{C}$ |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

## TO-247 (IXFH) Outline



Terminals: 1 - Gate  
2 - Drain  
3 - Source

| Dim.           | Millimeter |       | Inches |       |
|----------------|------------|-------|--------|-------|
|                | Min.       | Max.  | Min.   | Max.  |
| A              | 4.7        | 5.3   | .185   | .209  |
| A <sub>1</sub> | 2.2        | 2.54  | .087   | .102  |
| A <sub>2</sub> | 2.2        | 2.6   | .059   | .098  |
| b              | 1.0        | 1.4   | .040   | .055  |
| b <sub>1</sub> | 1.65       | 2.13  | .065   | .084  |
| b <sub>2</sub> | 2.87       | 3.12  | .113   | .123  |
| C              | .4         | .8    | .016   | .031  |
| D              | 20.80      | 21.46 | .819   | .845  |
| E              | 15.75      | 16.26 | .610   | .640  |
| e              | 5.20       | 5.72  | 0.205  | 0.225 |
| L              | 19.81      | 20.32 | .780   | .800  |
| L1             |            | 4.50  |        | .177  |
| ØP             | 3.55       | 3.65  | .140   | .144  |
| Q              | 5.89       | 6.40  | 0.232  | 0.252 |
| R              | 4.32       | 5.49  | .170   | .216  |
| S              | 6.15       | BSC   | .242   | BSC   |

## PRELIMINARY TECHNICAL INFORMATION


The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.


IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

|           |           |           |           |              |              |              |              |              |             |
|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
| 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
| 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 3. Output Characteristics @  $T_J = 150^\circ\text{C}$**




**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 80\text{A}$  Value vs. Junction Temperature**




**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 80\text{A}$  Value vs. Drain Current**




**Fig. 6. Drain Current vs. Case Temperature**




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**



**Fig. 11. Capacitance**



**Fig. 12. Forward-Bias Safe Operating Area**










**Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature**

**Fig. 14. Resistive Turn-on Rise Time vs. Drain Current**

**Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance**

**Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature**

**Fig. 17. Resistive Turn-off Switching Times vs. Drain Current**

**Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance**


Fig. 19. Maximum Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).