

LOCTITE EDAG 437 E&C

October 2014

PRODUCT DESCRIPTION

LOCTITE EDAG 437 E&C provides the following product characteristics:

Technology	Thermoplastic
Appearance	Copper
Operating Temperature	-40 to 95 °C
Product Benefits	• High conductivity • Ease of use • Burnish resistant • Excellent environmental resistance • High conductivity per μm dry coating • Compatible with commonly used plastics • Stable electrical properties after heat cycling
Cure	Room temperature cure
Application	Conductive coating
Typical Assembly Applications	Reflective coating on parabolic antennas and Plastic housing of consumer electronics and medical equipments

LOCTITE EDAG 437 E&C EMC shielding coating is designed to provide electromagnetic compatibility (EMC) in electronic equipment housing.

It is an extremely conductive copper coating that provides excellent shielding against radiated electro-magnetic interference (EMI) and protection against electrostatic discharge (ESD).

TYPICAL PROPERTIES OF UNCURED MATERIAL

Solids Content by Weight, %	63.5
Viscosity @ 20 °C, mPa·s (cP):	
Speed 20 rpm	4,500
Density, kg/cm ³	1,650
Theoretical coverage, m ² /kg:	
@ 10 μm coating thickness	23
Shelf Life @ 5 to 30°C, days	365
Flash Point, °C	23

TYPICAL PROPERTIES OF CURED MATERIAL

On Lexan panels, airdried overnight

Physical Properties

Attenuation @ 50 μm , dB	50 to 70
Adhesion	5B
Pencil hardness	>9H

Electrical Properties

Sheet Resistivity, ohms/sq:

@ 1 mil dry coating thickness

<0.5

GENERAL INFORMATION

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

DIRECTIONS FOR USE

1. Surface Preparation

- Surface to be coated must be dry and free on contaminants such as oil or chemical residues.

2. Mixing/Dilution

- Thoroughly mix LOCTITE EDAG 437 E&C before dilution. Normally, the product is diluted with MEK.
- Recommended dilution ratio(s) as follows:
By Volume: 5 part(s) product to 4 part(s) solvent
By Weight: 5 part(s) product to 2 part(s) solvent
- Complicated parts, such as those molded from solvent sensitive plastics (ABS, Polystyrene and Polycarbonate), are very prone to stress cracking. In such cases, replacing about 15% of the MEK with Isobutanol or Diacetone Alcohol (DAA) provides a suitable alternative.

3. Application

- LOCTITE EDAG 437 E&C should be applied by spray using conventional propeller agitated pressure pot spray systems.
- Small prototype runs may be sprayed with well-mixed product, using suction cup spray equipment.
- A nominal 50 to 75 μm dry coating thickness is recommended for good shielding performance. However, a thinner coating may be acceptable, depending on the shielding requirements of the device being protected.
- Avoid dry spraying for maximum adhesion and conductivity.

4. Drying

- LOCTITE EDAG 437 E&C dries to touch in about 5 minutes; to handle in approximately 30 minutes, depending on ambient temperature and coating thickness.
- LOCTITE EDAG 437 E&C reaches full coating properties after air drying overnight.

5. Cleanup

- For high volume production where masks are used to prevent coating certain areas, the masks can be cleaned with esters (butylacetate, ethylacetate) or ketones (MIBK, MEK) solvents.
- Spray or mixing equipment may be cleaned with the same solvents.

Storage

Store product in the unopened container in a cool dry well ventilated area. Storage information may be indicated on the product container labeling.

Optimal Storage : 5 to 30 °C

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Empty containers may retain hazardous properties.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Conversions

$$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$$

$$\text{kV/mm} \times 25.4 = \text{V/mil}$$

$$\text{mm} / 25.4 = \text{inches}$$

$$\text{N} \times 0.225 = \text{lb}$$

$$\text{N/mm} \times 5.71 = \text{lb/in}$$

$$\text{N/mm}^2 \times 145 = \text{psi}$$

$$\text{MPa} = \text{N/mm}^2$$

$$\text{MPa} \times 145 = \text{psi}$$

$$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$$

$$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$$

$$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$$

$$\text{mPa}\cdot\text{s} = \text{cP}$$

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1

Americas
+1.888.943.6535

Europe
+32.1457.5611

Asia
+86.21.3898.4800

For the most direct access to local sales and technical support visit: www.henkel.com/electronics