



AB-FQVVV06-19712-XA1

Constant Voltage, IP67, Silicone Cover Square Rope Light, 197", RGB

Features:

- UL listed
- IP67 waterproof rating
- Top emitting, wide viewing angle 120°
- Operating temperature -40°C~85°C
- Storage temperature -40°C~85°C
- Environment humidity 40-70%RH

Application:

- Conference/Meeting rooms
- Factories and Offices
- Commercial Purposes
- Residential/Institution Buildings
- Schools
- Hospitals

Product performance parameter:

Serial number	Part Number	Color temperature	nm	QTY/M (39.3in)	Luminous per meter	Efficacy	working voltage IF(V)	Rated power (W/M)
1	AB-FQ01206-19712-XA1	Red	520-530nm	120LED	77lm	11lm	12V/0.6A	7
		Green	620-630nm		176lm	32lm	12V/0.44A	5.5
		Blue	460-470nm		44lm	8lm	12V/0.44A	5.5
2	AB-FQ02406-19712-XA1	Red	520-530nm	120LED	77lm	11lm	24V/0.3A	7
		Green	620-630nm		176lm	32lm	24V/0.22A	5.5
		Blue	460-470nm		44lm	8lm	24V/0.22A	5.5


Notes :

1. Luminous flux plus or minus 10% is allowed in the floating.
2. Maximum length current attenuation 15%.
3. Photometric standards are based on CIE eye sensitivity curve diagram test.




Schematic diagram:

Schematic:






Product size chart:




1. MATERIAL: SILICONE, DUROMETER: SHORE A 60~65 OR EQUAL MATERIAL
2. UNIT: MM(IN)
3. COLOR: WHITE

Maximum Flexibility Precaution





Product packaging



Model	Part number	box(pcs)	Ret Weight/box	Gross Weight/box
1	AB-FQVVV06-19712-XA1			