



#### Description

- Temperature compensated crystal oscillator (TCXO) in a hermetically sealed 3.2x2.5mm SMD package.
- Model IQXT-220-1
- Model Issue number 3

#### Frequency Parameters

- Frequency 10.0MHz
- Frequency Tolerance  $\pm 1.00$ ppm
- Frequency Stability  $\pm 0.28$ ppm
- Operating Temperature Range  $-40.00$  to  $85.00^{\circ}\text{C}$
- Ageing  $\pm 0.02$ ppm max/day,  $\pm 1$ ppm max/year
- Frequency Tolerance: Measurement referenced to frequency observed with  $T_A=25^{\circ}\text{C}$ ,  $V_s=3.3\text{V}$  and load= $10\text{k}\Omega//10\text{pF}$ , within 30 days after ex-works.
- Frequency Stability:  $T_A$  varied across the operating temperature range, measurement referenced to frequency observed with  $f_{\text{ref}}=(f_{\text{max}}+f_{\text{min}})/2$ ,  $V_s=3.3\text{V}$ , load= $10\text{k}\Omega//10\text{pF}$  and temperature variable speed less than  $2^{\circ}\text{C}/\text{min}$ .
- Ageing:  $V_s$ ,  $T_A$  and load constant, measurement referenced to frequency observed with  $T_A=25^{\circ}\text{C}$ ,  $V_s=3.3\text{V}$ , load= $10\text{k}\Omega//10\text{pF}$  and after 1hr of operation.
- Supply Voltage Variation (measurement referenced to frequency observed  $T_A=25^{\circ}\text{C}$ ,  $V_s$  varied from  $3.13\text{V}$  to  $3.47\text{V}$  and load= $10\text{k}\Omega//10\text{pF}$ ):  $\pm 0.1$ ppm max
- Load Variation (measurement referenced to frequency observed with  $T_A=25^{\circ}\text{C}$ ,  $V_s=3.3\text{V}$  and load change= $10\text{k}\Omega//10\text{pF} \pm 5\%$ ):  $\pm 0.1$ ppm max

#### Electrical Parameters

- Supply Voltage  $3.3\text{V} \pm 5\%$
- Current Draw  $5.000\text{mA}$
- Current Consumption (@  $T_A=25^{\circ}\text{C}$ ,  $V_s=3.3\text{V}$  and load= $10\text{k}\Omega//10\text{pF}$ ):  $5\text{mA}$  max


#### Output Details

- Output Compatibility Clipped Sine
- Drive Capability  $10\text{k}\Omega//10\text{pF}$
- Output Voltage Level:  $0.8\text{V}$  pk-pk min

#### Noise Parameters

- Phase Noise @  $25^{\circ}\text{C}$  ( $F=10.0\text{MHz}$ , typ):
  - 90dBc/Hz @ 10Hz
  - 120dBc/Hz @ 100Hz
  - 140dBc/Hz @ 1kHz
  - 145dBc/Hz @ 10kHz
  - 148dBc/Hz @ 100kHz

#### Outline (mm)



#### Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

#### Environmental Parameters

- Operable Temperature Range: -40 to 85°C
- Storage Temperature Range: -55 to 105°C
- ESD Levels:
  - ESD Human Body Model (JEDEC JS-001-2010): Class 2: 2000V to 4000V
  - ESD Machine Model (JEDEC JESD22-A115C): Class B: 200V to 400V
- Shock: IEC 60068-2-27, Test Ea, Severity 50A: 100G acceleration for 6ms, half sine wave, 3 times in 3 mutually perpendicular planes.
- Vibration: IEC 60068-2-06, Test Fc: 10Hz-2000Hz, 0.75mm amplitude, 10G acceleration, 30mins per cycle, 3 times in 3 mutually perpendicular planes, test duration 2hrs.

#### Manufacturing Details

- Storage Conditions:
  - Temperature: -10 to 35°C
  - Humidity: 20 to 70% RH
- RoHS Terminations                      Ni (1µm~9µm), Au (0.5µ~1µm)
- RoHS Reflow Temp                        260°C max for 30sec max

#### Compliance

- RoHS Status (2015/863/EU)            Compliant
- REACH Status                                Compliant
- MSL Rating (JDEC-STD-033):            1

#### Packaging Details

- Tape & reel in accordance with EIA-481  
Quantities below the standard reel size to be supplied on cut tape  
  
Standard Pack Quantity: 3,000

---

#### Sales Office Contact Details:

UK: +44 (0)1460 270200

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)