

Enhancement Mode Field Effect Transistor

N-Channel

2N7002W

Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Ultra-Small Surface Mount Package
- These Devices are Pb-Free and are RoHS Compliant

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V_{DS}	60	V
Drain-Gate Voltage $R_{GS} \leq 1.0 \text{ M}\Omega$	V_{DGR}	60	V
Gate-Source Voltage Continuous Pulsed	V_{GSS}	± 20 ± 40	V
Gate-Source Voltage Continuous Continuous @ 100°C Pulsed	I_D	115 73 800	mA
Junction and Storage Temperature Range	T_J, T_{STG}	-55 to $+150$	$^\circ\text{C}$



Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Parameter	Symbol	Max	Unit
Total Device Dissipation Derating above $T_A = 25^\circ\text{C}$	P_D	200 1.6	MW mW/ $^\circ\text{C}$
Thermal Resistance, Junction-to-Ambient (Note 1)	$R_{\theta JA}$	625	$^\circ\text{C}/\text{W}$


1. Device mounted on FR-4 PCB, 1 inch $\times$ 0.85 inch $\times$ 0.062 inch. Minimum land pad size.

SIMPLIFIED SCHEMATIC



SC-70
CASE 419AB

MARKING DIAGRAM & PIN ASSIGNMENT



2N = Device Code
M = Date Code

ORDERING INFORMATION

Device	Package	Shipping [†]
2N7002W	SC-70 (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

2N7002W

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
-----------	--------	----------------	-----	-----	-----	-------

OFF CHARACTERISTICS (Note 2)

Drain–Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0 V, I _D = 10 μA		60	78	–	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V, V _{DS} = 60 V	T _C = 25°C	–	0.001	1.0	μA
			T _C = 125°C	–	7	500	
Gate–Body Leakage Current	I _{GSS}	V _{GS} = ±20 V, V _{DS} = 0 V		–	0.2	±10	nA

ON CHARACTERISTICS (Note 2)

Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS} = V_{DS}, I_D = 250\text{ }\mu\text{A}$	1.0	1.76	2.0	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = 5\text{ V}, I_D = 0.05\text{ A}$	–	1.6	7.5	Ω
		$V_{GS} = 10\text{ V}, I_D = 0.5\text{ A}, @ T_J = 125^\circ\text{C}$	–	2.53	13.5	
On-State Drain Current	$I_{D(on)}$	$V_{GS} = 10\text{ V}, V_{DS} = 7.5\text{ V}$	0.5	1.43	–	A
Forward Transconductance	g_{FS}	$V_{DS} = 10\text{ V}, I_D = 0.2\text{ A}$	80	356.5	–	mS

DYNAMIC CHARACTERISTICS

Input Capacitance	C_{ISS}	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1.0\text{ MHz}$	–	37.8	50	pF
Output Capacitance	C_{OSS}		–	12.4	25	
Reverse Transfer Capacitance	C_{RSS}		–	6.5	7.0	

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{D(on)}$	$V_{GEN} = 10\text{ V}, V_{DD} = 30\text{ V}, I_D = 0.2\text{ A},$ $R_L = 150\text{ }\Omega, R_{GEN} = 25\text{ }\Omega$	–	5.85	20	ns
Turn-Off Delay Time	$t_{D(off)}$		–	12.5	20	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Short duration test pulse used to minimize self-heating effect.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Gate Voltage and Drain Current




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Gate-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Gate Threshold Variation with Temperature

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 7. Reverse Drain Current Variation with Diode Forward Voltage and Temperature






Figure 8. Power Derating




SC-70, 3 Lead, 1.25x2
CASE 419AB
ISSUE A


DATE 13 FEB 2023




TOP VIEW



SIDE VIEW



END VIEW



SOLDERING FOOTPRINT

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES IN DEGREES.
2. COMPLIES WITH JEDEC MO-203

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.80		1.10
A1	0.00		0.10
A2	0.80	0.90	1.00
b	0.15		0.30
c	0.08		0.22
D	1.80	2.00	2.20
E	1.80	2.10	2.40
E1	1.15	1.25	1.35
e	0.65 BSC		
L	0.26	0.36	0.46
L1	0.42 REF		
Θ	0°		8°
Θ1	4°		10°

* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON34256E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	SC-70, 3 LEAD, 1.25X2	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales