


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-3-308/199_N

Properties

- Excellent corrosion resistance in a wide range of environments
- High salt mist resistant
- Material 316L stainless steel
- Excellent return loss values
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Body	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	14 g
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	soldered

Environmental data

Operation temperature	-65 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)
11_SMA-50-3-308/199_N

Ordering Information Table		
Item number	Item description	Packaging type
85117587	11_SMA-50-3-308/199_NH	Bulk 100 pcs
Suitable cables		
Cable group	Y27 - 3mm / 50 Ohm	
	Y25 - 3mm / 50 Ohm	
Suitable cables	MULTIFLEX_141_CT	
	SUCOFORM_141_CT	
Additional Information		
Remarks	Dos not fit to EZ_141_CT !	
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P27582 / Date of publication: 30.10.2024 / uncontrolled copy