

COAXIAL ADAPTER, SMA - TNC, 50 Ohm, plug / jack (male / female)
33_SMA-TNC-50-1/1--_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CECC 22110
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz
VSWR	DC - 6 GHz (≤ 1.03 + 0.05 f GHz)

COAXIAL ADAPTER, SMA - TNC, 50 Ohm, plug / jack (male / female)
33_SMA-TNC-50-1/1--_N

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
6 GHz ... 11 GHz		17 dB	1.33
Mechanical data			
Weight		0.0087 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-65 °C ... 165 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22640939	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22640939	33_SMA-TNC-50-1/1--_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2146 / Date of publication: 12.07.2025 / uncontrolled copy