

COAXIAL ADAPTER, TNC - SMA, 50 Ohm, plug / jack (male / female)

33_TNC-SMA-50-1/1--_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
TNC	plug (male)	IEC 60169-17_MIL-STD-348A/313_CECC 22200
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	26.4 dB	1.1

COAXIAL ADAPTER, TNC - SMA, 50 Ohm, plug / jack (male / female)
33_TNC-SMA-50-1/1--_U

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
4 GHz ... 8 GHz	20.8 dB	1.2
8 GHz ... 11 GHz	17.7 dB	1.3
Mechanical data		
Weight	0.0147 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22640940	33_TNC-SMA-50-1/1--_UE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2136 / Date of publication: 27.05.2024 / uncontrolled copy