


COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.00.0037

Properties

- Slim in-line design
- Broadband operation from DC up to 6 GHz
- DC continuity for remote powering
- Permanently installed gas discharge tube



Product configuration	
Main path connectors	Port 1: protected, N jack (female) Port 2: unprotected, SMA jack (female)
Mounting and grounding	MH12 (bulkhead mounting)
Side of bulkhead	protected side
Inline design	YES
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Bronze / Gold Plating Port 2: Copper Beryllium Alloy / Gold Plating

Electrical data	
Impedance	50 Ω
Frequency frame	0 MHz to 3000 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.2 dB
CW power frame	≤ 30 W
Static spark voltage	200 V, +/- 25 % (@ 100 V/s)
Residual pulse energy (typ.)	350 μ J (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Surge current handling capability	10 kA single, 5 kA multiple (test pulse 8/20 μ s)

Electrical bands	
Frequency range	0 MHz ... 2000 MHz
Return loss typical	≥ 23 dB
Insertion loss	≤ 0.2 dB
Power avg. / peak	≤ 30 W / ≤ 30 W

COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.00.0037

Electrical remarks			
Gas tube		Yes DC, GDT included, not replaceable	
Mechanical data			
Weight		54 g	
Mating cycles		500	
Environmental data			
Operation temperature		-40 °C ... 85 °C	
Storage temperature		-40 °C ... 85 °C	
Ingress protection (IP Rating)		Unmated / IP68, according to IEC 60529	
Ingress protection (comment)		Only N connector side	
Thermal shock according		MIL-STD-202, Method 107, Cond. B	
Vibration according		MIL-STD-202, Method 204, Cond. D	
Moisture resistance according		MIL-STD-202, Method 106	
Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85115151	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number		Item description	
85115151		3406.00.0037	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P50128 / Date of publication: 01.03.2025 / uncontrolled copy