

PFC SPM[®] 3 Series for 2-Phase Bridgeless PFC

FPDB60PH60B

General Description

The FPDB60PH60B is an advanced PFC SPM 3 module providing a fully-featured, high-performance Bridgeless PFC (Power Factor Correction) input power stage for consumer, medical, and industrial applications. These modules integrate optimized gate drive of the built-in IGBTs to minimize EMI and losses, while also providing multiple on-module protection features including under-voltage lockout, over-current shutdown, thermal monitoring, and fault reporting. These modules also feature high-performance output diodes and shunt resistor for additional space savings and mounting convenience.

Features

- UL Certified No. E209204 (UL1557)
- 600 V – 60 A 2-Phase Bridgeless PFC with Integral Gate Driver and Protection
- Very Low Thermal Resistance Using AlN DBC Substrate
- Built-in NTC Thermistor for Temperature Monitoring
- Built-in Shunt Resistor for Current Sensing
- Optimized for 20 kHz Switching Frequency
- Isolation Rating: 2500 V_{rms} / min
- This is a Pb-Free Device

Applications


- 2-Phase Bridgeless PFC Converter

Related Source

- [AN-9041 – Bridgeless PFC SPM 3 Series Design Guide](#)

Integrated Drive, Protection and System Control Functions


- For IGBTs: Gate Drive Circuit, Over-Current Protection (OCP), Control Supply Circuit Under-Voltage Lock-Out (UVLO) Protection
- Fault Signal: Corresponding to OC and UV Fault
- Built-in Thermistor: Temperature Monitoring
- Input Interface: Active-HIGH Interface, Works with 3.3 / 5 V Logic, Schmitt-trigger Input



3D Package Drawing
(Click to Activate 3D Content)

SPMCA-027 / PDD STD, SPM27-CA, DBC TYPE
CASE MODFJ

MARKING DIAGRAM



&Z = Assembly Plant Code
 &K = 2-Digits Lot Run Traceability Code
 &3 = 3-Digit Date Code
 FPDB60PH60B = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 9 of this data sheet.

FPDB60PH60B

PIN CONFIGURATION





Figure 1. Pin Configuration – Top View

PIN DESCRIPTIONS

Pin No.	Pin Name	Pin Description
1	V _{CC}	Common Bias Voltage for IC and IGBTs Driving
2	COM	Common Supply Ground
4	IN _(R)	Signal Input for Low-Side R-Phase IGBT
5	IN _(S)	Signal Input for Low-Side S-Phase IGBT
6	V _{FO}	Fault Output
7	C _{FOD}	Capacitor for Fault Output Duration Selection
8	C _{SC}	Capacitor(Low-Pass Filter) for Over-Current Detection
19	R _(TH)	Series Resistor for The Use of Thermistor
20	V _(TH)	Thermistor Bias Voltage
21	V _{AC-}	Current Sensing Terminal
22	N _{SENSE}	Current Sensing Reference Terminal
24	N	Negative Rail of DC-Link
25	R	Output for R-Phase
26	S	Output for S-Phase
27	P _R	Positive Rail of DC-Link
3, 9 ~ 18, 23	NC	No Connection

FPDB60PH60B

INTERNAL EQUIVALENT CIRCUIT AND INPUT/OUTPUT PINS



NOTE:

1. Converter is composed of two IGBTs including four diodes and one IC which has gate driving and protection functions.

Figure 2. Internal Block Diagram

FPDB60PH60B

ABSOLUTE MAXIMUM RATINGS ($T_J = 25^{\circ}\text{C}$ unless otherwise specified)

Symbol	Parameter	Conditions	Rating	Unit
INVERTER PART				
V_i	Supply Voltage	Applied between R – S	264	V_{rms}
$V_{i(Surge)}$	Supply Voltage (Surge)	Applied between R – S	500	V
V_{PN}	Output Voltage	Applied between P – N	450	V
$V_{PN(Surge)}$	Output Voltage (Surge)	Applied between P – N	500	V
V_{CES}	Collector – Emitter Voltage		600	V
$\pm I_C$	Each IGBT Collector Current	$T_C = 25^{\circ}\text{C}$	60	A
$\pm I_{CP}$	Each IGBT Collector Current (Peak)	$T_C = 25^{\circ}\text{C}$, Under 1 ms Pulse Width	90	A
P_C	Collector Dissipation	$T_C = 25^{\circ}\text{C}$ per IGBT	178	W
V_{RRM}	Repetitive Peak Reverse Voltage		600	V
I_{FSM}	Peak Forward Surge Current	Single Half Sine-Wave	350	A
P_{RSH}	Power Rating of Shunt Resistor	$T_C < 125^{\circ}\text{C}$	2	W
T_J	Operating Junction Temperature	(Note 2)	-40 ~ 150	$^{\circ}\text{C}$

CONTROL PART

V_{CC}	Control Supply Voltage	Applied between V_{CC} – COM	20	V
V_{IN}	Input Signal Voltage	Applied between IN – COM	-0.3 ~ 17.0	V
V_{FO}	Fault Output Supply Voltage	Applied between V_{FO} – COM	-0.3 ~ $V_{CC} + 0.3$	V
I_{FO}	Fault Output Current	Sink Current at V_{FO} pin	5	mA
V_{SC}	Current-Sensing Input Voltage	Applied between C_{SC} – COM	-0.3 ~ $V_{CC} + 0.3$	V

TOTAL SYSTEM

T_C	Module Case Operation Temperature		-30 ~ 100	$^{\circ}\text{C}$
T_{STG}	Storage Temperature		-40 ~ 150	$^{\circ}\text{C}$
V_{ISO}	Isolation Voltage	60 Hz, Sinusoidal, AC 1 Minute, Connect Pins to Heat-Sink Plate	2500	V_{rms}

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

2. The maximum junction temperature rating of the power chips integrated within the PFC SPM product is 150°C (@ $T_C \leq 100^{\circ}\text{C}$).

THERMAL RESISTANCE

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$R_{\theta(j-c)Q}$	Junction to Case Thermal Resistance (Referenced to PKG Center)	IGBT	–	–	0.7	$^{\circ}\text{C}/\text{W}$
$R_{\theta(j-c)HD}$		High-Side Diode	–	–	1.5	$^{\circ}\text{C}/\text{W}$
$R_{\theta(j-c)LD}$		Low-Side Diode	–	–	0.85	$^{\circ}\text{C}/\text{W}$

3. For the measurement point of case temperature (T_C), please refer to Figure 1.

FPDB60PH60B

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
CONVERTER PART						
V _{CE(SAT)}	IGBT Saturation Voltage	V _{CC} = 15 V, V _{IN} = 5 V, I _C = 50 A	–	2.0	2.5	V
V _{FH}	High-Side Diode Voltage	I _F = 50 A	–	2.4	2.9	V
V _{FL}	Low-Side Diode Voltage	I _F = 50 A	–	1.2	1.6	V
t _{ON}	Switching Times	V _{PN} = 400 V, V _{CC} = 15 V, I _C = 60 A, V _{IN} = 0 V ↔ 5 V, Inductive load (Note 4)	–	560	–	ns
t _{C(ON)}			–	270	–	ns
t _{OFF}			–	520	–	ns
t _{C(OFF)}			–	110	–	ns
t _{rr}			–	44	–	ns
I _{rr}			–	6.5	–	A
R _{SENSE}	Current-Sensing Resistor		1.8	2.0	2.2	mΩ
I _{CES}	Collector – Emitter Leakage Current	V _{CE} = V _{CES}	–	–	250	μA

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. t_{ON} and t_{OFF} include the propagation delay time of the internal drive IC. t_{C(ON)} and t_{C(OFF)} are the switching times of IGBT itself under the given gate driving condition internally. For the detailed information, please see Figure 3.




Figure 3. Switching Time Definition

FPDB60PH60B

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified.) (continued)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
CONTROL PART						
I _{QCCL}	Quiescent V _{CC} Supply Current	V _{CC} = 15 V, I _N = 0 V V _{CC} – COM	–	–	26	mA
V _{FOH}	Fault Output Voltage	V _{SC} = 0 V, V _{FO} Circuit: 4.7 kΩ to 5 V Pull-up	4.5	–	–	V
V _{FOL}		V _{SC} = 1 V, V _{FO} Circuit: 4.7 kΩ to 5 V Pull-up	–	–	0.8	V
V _{SC(ref)}	Short Circuit Trip Level	V _{CC} = 15 V	0.45	0.50	0.55	V
UV _{CCD}	Supply Circuit Under-Voltage Protection	Detection level	10.7	11.9	13.0	V
UV _{CCR}		Reset level	11.2	12.4	13.2	V
t _{FOD}	Fault-Out Pulse Width	C _{FOD} = 33 nF (Note 5)	1.4	1.8	2.0	ms
V _{IN(ON)}	ON Threshold Voltage	Applied between IN – COM	3.0	–	–	V
V _{IN(OFF)}	OFF Threshold Voltage		–	–	0.8	V
R _{TH}	Resistance of Thermistor	At T _C = 25°C (See Figure 4)	–	50	–	kΩ
		At T _C = 80°C (See Figure 4)	–	5.76	–	kΩ

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. The fault-out pulse width t_{FOD} depends on the capacitance value of C_{FOD} according to the following approximate equation:

$$C_{FOD} = 18.3 \times 10^{-6} \cdot t_{FOD}[F]$$




Figure 4. R-T Curve of the Built-in Thermistor

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V _I	Input Supply Voltage	Applied between R – S	180	–	264	V _{rms}
V _{PN}	Output Voltage	Applied between P – N	–	280	400	V
V _{CC}	Control Supply Voltage	Applied between V _{CC} – COM	13.5	15	16.5	V
dV _{CC} / dt	Control Supply Variation	Applied between IN – COM	–1	–	1	V/μs
f _{PWM}	PWM Input Signal	T _C ≤ 100°C, T _J ≤ 125°C, per IGBT	–	20	–	kHz

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

FPDB60PH60B

MECHANICAL CHARACTERISTICS AND RATINGS

Item	Conditions		Min	Typ	Max	Unit
Mounting Torque	Mounting Screw: M3	Recommended 0.62 N•m	0.51	0.62	0.72	N•m
Device Flatness	See Figure 5		0	–	+120	μm
Weight			–	15.00	–	g






Figure 5. Flatness Measurement Position

TIME CHARTS OF PROTECTIVE FUNCTION



- P1: Normal operation: IGBT ON and conducting current.
P2: Under-voltage detection.
P3: IGBT gate interrupt.
P4: Fault signal generation.
P5: Under-voltage reset.
P6: Normal operation: IGBT ON and conducting current.


Figure 6. Under-Voltage Protection



- P1: Normal operation: IGBT ON and conducting current.
P2: Over Current detection.
P3: IGBT gate interrupt / fault signal generation.
P4: IGBT is slowly turned off.
P5: IGBT OFF signal.
P6: IGBT ON signal: but IGBT cannot be turned on during the fault output activation.
P7: IGBT OFF state.
P8: Fault output reset and normal operation start.

Figure 7. Over-Current Protection

FPDB60PH60B



NOTE:

6. For the over-current protection, please set time constant in the range 3 ~ 4 μ s.

Figure 8. Application Example


PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package	Shipping
FPDB60PH60	FPDB60PH60B	SPMCA-027 / PDD STD, SPM27-CA, DBC TYPE (Pb-Free / Halide Free)	60 Units / Tube

SPM is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

SPMCA-027 / PDD STD, SPM27-CA, DBC TYPE
CASE MODFJ
ISSUE Q

DATE 31 JAN 2017










LEAD PITCH (TOLERANCE : ± 0.30)

A : 1.778

B : 2.050

C: 2.531



NOTES: UNLESS OTHERWISE SPECIFIED

A) THIS PACKAGE DOES NOT COMPLY
TO ANY CURRENT PACKAGING STANDARD

B) ALL DIMENSIONS ARE IN MILLIMETERS
C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS

D) () IS REFERENCE

LAND PATTERN RECOMMENDATIONS

DOCUMENT NUMBER:	98AON13563G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	SPMCA-027 / PDD STD, SPM27-CA, DBC TYPE	PAGE 1 OF 1

onsemi and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales