

COAXIAL ADAPTER, 7/16, 50 Ohm, T-style, 3 jacks (female)

46_716-50-0-1/003_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data

7/16		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
7/16		
Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	7.5 GHz

Mechanical data

Weight	0.2589 kg
Mating cycles	500

COAXIAL ADAPTER, 7/16, 50 Ohm, T-style, 3 jacks (female)
46_716-50-0-1/003_-

Environmental data	
Operation temperature	-65 °C ... 165 °C

Ordering Information Table		
Item number	Item description	Packaging type
22643266	46_716-50-0-1/003_-E	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1902 / Date of publication: 12.04.2024 / uncontrolled copy