

Precision Attenuator, Low Power

6820.17.B

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.



Product configuration		
Interface	Gender	Standard
N-precision	plug (male)	IEC 60169-16_MIL-STD-348A/304_CECC 22210
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/304_CECC 22210

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 18 GHz
Attenuation nominal	20 dB

Electrical Data (frequency related)		
Frequency range	Attenuation deviation	VSWR max
0 GHz to 4 GHz	0.3 dB	1.1
4 GHz to 6 GHz	0.3 dB	1.1
6 GHz to 8 GHz	0.5 dB	1.15
8 GHz to 12.4 GHz	0.5 dB	1.15
12.4 GHz to 18 GHz	0.8 dB	1.25

Electrical Data (power)	
Average power	1 W at 30 °C ambient temperature. Linearly derated to 0 W at 130 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 0.05 % duty cycle
Electrical remarks	Peak voltage max. 160V (50 Ohm)

Interface and material data		
Interface	N-precision / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating

Precision Attenuator, Low Power
6820.17.B

Interface and material data		
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Interface	N-precision / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	

Mechanical data	
Weight	0.086 kg

Environmental data	
Operation temperature	-55 °C ... 130 °C

Ordering Information Table	
Item number	Item description
22550191	6820.17.B

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P37990 / Date of publication: 21.11.2024 / uncontrolled copy