

COAXIAL FIXED ATTENUATOR, 75 Ohm, 6 dB, BNC

6906.02.A

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.

**Product configuration**

Interface	Gender	Standard
BNC	plug (male)	IEC 60169-8_MIL-STD-348A/301_CECC 22120
BNC	jack (female)	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Electrical data

Impedance	75Ω
Operating frequency	0 GHz ... 1 GHz
Attenuation nominal	6 dB
Return loss	20.8 dB

Electrical Data (frequency related)

Frequency range	Attenuation deviation	VSWR max
0 GHz to 0.5 GHz	+/- 0.3 dB	1.1
0.5 GHz to 0.7 GHz	+/- 0.3 dB	
0.7 GHz to 1 GHz	+/- 0.8 dB	

Electrical Data (power)

Average power	1 W at 30 °C ambient temperature. Linearly derated to 0 W at 130 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 0.05 % duty cycle
Electrical remarks	Peak voltage max. 160V (50 Ohm)

Interface and material data

Interface	BNC / plug (male)	
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating

COAXIAL FIXED ATTENUATOR, 75 Ohm, 6 dB, BNC
6906.02.A

Interface and material data		
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Interface	BNC / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Mechanical data	
Weight	0.025 kg

Environmental data	
Operation temperature	-55 °C ... 130 °C

Ordering Information Table	
Item number	Item description
22550088	6906.02.A

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1599 / Date of publication: 21.11.2024 / uncontrolled copy