

RG174, 50 Ohm, 1 GHz, 85°C, Ø2.55 mm, PVC jacket

RG_174_/U

Properties

- Mil standard RG cable
- Excellent RF performance for precision applications
- Suitable for use in application up to 1 GHz



Construction			
Component	Material	Detail	Diameter
Centre conductor	Steel, Copper plated	Strand-07, 87%	0.48 mm - 0.13 mm
Dielectric	PE (Polyethylene)		1.48 mm
Outer conductor	Copper, Tin plated	Braid, 87%	2 mm
Jacket	PVC II (low migration)	RAL 9005 - bk	2.55 mm +/- 0.13 mm

Electrical data	
Impedance	50 Ω +/- 2Ω
Operating frequency	≤ 1 GHz
Capacitance	101 pF/m
Velocity of signal propagation	66 %
Signal delay	5.03 ns/m
Screening effectiveness	40 dB at frequency 0.001 GHz ... 1GHz
Insulation resistance	100000000 MΩ*m
Operating Voltage (at sea level)	≤ 1.5 kVrms
Test voltage (50 Hz/1 min)	≤ 3 kVrms

Mechanical data	
Weight	approx. 11.2 g/m
Static bending radius	≥ 15 mm
Repeated bending radius	26 mm

Environmental data	
Operation temperature	-25 °C ... 85 °C
Installation temperature	-20 °C ... 60 °C
Fire characteristics	contains halogene

RG174, 50 Ohm, 1 GHz, 85°C, Ø2.55 mm, PVC jacket
RG_174_/U

Additional Information	
MIL reference: M17/196-00001 (former reference: M17/119-RG174)	

Suitable connectors	
Cable group	U2

Ordering information		
Item number	Item description	Available as assembly only
22510040	RG_174_/U	No

Power Matrix			
Calculation: typical Attenuation [formula: (a*f^0.5 + b*f)] and maximum Power CW [formula: (p/f^0.5)]			
a coefficient typical =	0.888	b coefficient typical =	0.034
fmax =	1.0	P at 1 GHz =	37.0
Frequency	Nom. attenuation	Nom. attenuation	CW power
GHz	(dB/m)	(dB/ft)	(W)
	sea level 25°C ambient temperature	sea level 25°C ambient temperature	sea level 40°C ambient temperature
0.10	0.284	0.087	117
0.20	0.404	0.123	83
0.30	0.497	0.151	68
0.40	0.575	0.175	59
0.60	0.708	0.216	48
0.80	0.821	0.250	41
1.00	0.922	0.281	37

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P977 / Date of publication: 08.08.2024 / uncontrolled copy