

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)

11_BNC-50-4-33/12-_N

Properties

- Suitable for use with Eacon_4C cable
- Applicable in frequencies up to 4 GHz
- Compliant with MIL-STD-348A/301 interface standard



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Bronze	Nickel Plating
Body	Bronze	Nickel Plating
Other body part	Stainless steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	Nickel Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	23 dB	1.15

Mechanical data	
Weight	0.0221 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)

11_BNC-50-4-33/12-_N

Environmental data	
Operation temperature	-60 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84139633	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84139633	11_BNC-50-4-33/12-_NE	Single

Suitable cables	
Cable group	U94 - EACON_4C
Suitable cables	EACON_4C

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades
22642718	74_Z-0-0-12	Knives / Blades
84079184	74_Z-0-0-473	Cable stripping tool
84078907	74_Z-0-0-474	Trimming tool
85012794	74_Z-0-0-616	
84079183	74_Z-0-0-476	
84079191	74_Z-0-0-475	
84079187	74_Z-0-0-479	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3686 / Date of publication: 12.07.2025 / uncontrolled copy