


COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-23-43/033_-

Properties

- Field mountable connector series Quick-fit
- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Interface type	Gender	Standard
N	plug	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	EP (Epoxy)
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	30 dB	1.07
2.5 GHz ... 3 GHz	28 dB	1.08

Mechanical data	
Weight	0.19 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable plug (male)

11_N-50-23-43/033_-

Environmental data	
Operation temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP68 (24 h of water, 1 m)

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84124063	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering Information Table		
Item number	Item description	Packaging type
84124063	11_N-50-23-43/033_-E	Single

Suitable cables	
Cable group	M25 - 23 mm / 50 Ohm
	M24 - 22 mm / 50 Ohm
	M23 - 22 mm / 50 Ohm
Suitable cables	SUCOFEEED_7/8_LW_LA
	SUCOFEEED_7/8_LA
	SUCOFEEED_7/8

Additional Information	
Remarks	Stripping tools: 85002265 74_Z-0-23-21 for 7/8" & 7/8"HF 84147229 74_Z-0-23-22 for 7/8" LA
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
84147229	74_Z-0-23-22	Cable stripping tool
85002265	74_Z-0-23-21	Cable stripping tool
84133924	74_Z-0-23-100	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3598 / Date of publication: 12.07.2025 / uncontrolled copy