

COAXIAL CONNECTOR, PC 1.85, 50 Ohm, Straight cable plug (male)
11_PC185-50-2-5/19-_NE

Properties

- Best electrical performance and excellent mechanical stability
- Extreme reliability
- Particularly well suited for semi-rigid, semi-flex and flexible cable
- Mechanical intermateable with PC 1.85 (1.85 mm standard)



Product configuration		
Interface type	Gender	Standard
PC 1.85	plug	IEC 61169-32

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer conductor	Stainless steel	Passivated (Plating)
Body	Stainless steel	Passivated (Plating)
Insulator	LCP (Liquid crystal polymer)	
Coupling nut	Stainless steel	Passivated (Plating)

Electrical data	
Impedance	50 Ω
Interface frequency	67 GHz

Mechanical data	
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	soldered

Environmental data	
Operation temperature	-55 °C ... 125 °C

COAXIAL CONNECTOR, PC 1.85, 50 Ohm, Straight cable plug (male)

11_PC185-50-2-5/19-_NE

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84152948	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84152948	11_PC185-50-2-5/19-_NE	Single

Suitable cables	
Cable group	U99 - Customer specific

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3543 / Date of publication: 12.07.2025 / uncontrolled copy