


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-3-236/133_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 1 GHz	34 dB	1.04
1 GHz ... 2.5 GHz	32 dB	1.05
2.5 GHz ... 5 GHz	27 dB	1.09

Mechanical data

Weight	0.003 kg
Mating cycles	500
Cable entry centre contact	soldered

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-3-236/133_N

Mechanical data	
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84130702	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
84117821	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84130702	11_SMA-50-3-236/133_NE	Single
84117821	11_SMA-50-3-236/133_NP	Bulk 500 pcs

Suitable cables	
Cable group	U9 - 3 mm / 50 Ohm
	U41 - 3 mm / 50 Ohm
	U11 - 3 mm / 50 Ohm
Suitable cables	RADOX_RF_400
	G_03262_D
	ENVIROFLEX_400
Additional cables	RADOX_RF_400

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades
22544516	74_Z-0-0-55	Gauges
22543124	74_Z-0-0-14	Locator
85008389	76_Z-0-0-57	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3462 / Date of publication: 12.07.2025 / uncontrolled copy