


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-3-45/133_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0045 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male)

11_SMA-50-3-45/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22642239	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22645987	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22642239	11_SMA-50-3-45/133_NE	Single
22645987	11_SMA-50-3-45/133_NH	Bulk 100 pcs

Suitable cables	
Cable group	U7 - 3 mm / 50 Ohm
Suitable cables	RG_58_C/U
	GX_03272
	G_03232

Additional Information	
Remarks	El. Optimized for cable RG 58 C/U
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades
22544555	74_Z-0-0-54	Holders
22543124	74_Z-0-0-14	Locator

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3457 / Date of publication: 12.07.2025 / uncontrolled copy