

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male), High salt mist resistant (SS316L)

11_SMA-50-7-2/199_N

Properties

- Excellent corrosion resistance in a wide range of environments
- High salt mist resistant
- Material 316L stainless steel
- Excellent return loss values
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
SMA	plug	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Body	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel (high salt mist resistant)	Passivated (Plating)
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2 GHz	28 dB	1.08
2 GHz ... 4 GHz	24 dB	1.13
4 GHz ... 8 GHz	23 dB	1.15

Mechanical data	
Cable entry centre contact	soldered
Cable entry outer contact	crimped

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight cable plug (male), High salt mist resistant (SS316L)

11_SMA-50-7-2/199_N

Environmental data	
Installation temperature	-65 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85167341	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
85167341	11_SMA-50-7-2/199_NE	Single

Suitable cables	
Cable group	X32 - 7 mm / 50 Ohm
	U30 - 7 mm / 50 Ohm
Suitable cables	SPUMA_400-RS-FR
	SPUMA_400-FR-01

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P43633 / Date of publication: 12.07.2025 / uncontrolled copy