

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight cable plug (male)

11_TNC-50-3-116/133_U

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz



Product configuration

Interface type	Gender	Standard
TNC	plug	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	30 dB	1.065

Mechanical data

Weight	0.0138 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight cable plug (male)

11_TNC-50-3-116/133_U

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22658218	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22658218	11_TNC-50-3-116/133_UH	Bulk 100 pcs

Suitable cables	
Cable group	U7 - 3 mm / 50 Ohm
Suitable cables	RG_58_C/U
	G_03232

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3405 / Date of publication: 12.07.2025 / uncontrolled copy