

SENCITY® Urban 200

1399.17.0272

Properties

- High Gain Directional antenna for Cellular bands between 3300 MHz and 4200 MHz
- Gain of 11 dBi with dual slant +/-45° polarisation
- Half power beamwidth of 70° (horizontal) and 35° (vertical)
- Wall bracket is included. Pole bracket is sold as separate item (9091.99.0274)
- N female connector

**Electrical data**

	Band 1	Band 2
Frequency	3300 MHz ... 3800 MHz	3800 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω
VSWR	1.8	1.8
Gain	11 dBi	11 dBi
Gain	11 dBic	11 dBic
HPBW vertical	35 °	35 °
HPBW horizontal	70 °	70 °
Isolation between Ports	23 dB	22 dB
Front to back ratio	20 dB	20 dB
Co/Crosspolar Ratio	15 dB	15 dB
Ambient Temperature	25 °C	25 °C
Composite Power max	95 W	90 W

Electrical remarks

IMD level	-150 dBc at carrier power 2x 43 dBm
Remarks	Max power level per port is 95W in Band 1 Max power level per port is 90W in Band 2

Ports

	Port 1	Port 2	Port 3	Port 4
Port name	Cellular 1	Cellular 2	Cellular 3	Cellular 4
Connector	N, jack (female)	N, jack (female)	N, jack (female)	N, jack (female)
Polarization	-45° slant	+45° slant	-45° slant	+45° slant

SENCITY® Urban 200

1399.17.0272

Ports				
	Port 1	Port 2	Port 3	Port 4
DC grounded	No	No	No	

Connections				
	Port 1	Port 2	Port 3	Port 4
Port name	Cellular 1	Cellular 2	Cellular 3	Cellular 4
Band 1	✓	✓	✓	✓
Band 2	✓	✓	✓	✓

Mechanical data	
Weight	0.59 kg
Dimensions	184.8 mm x 164.6 mm x 84.2 mm (Height x Width x Depth)

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7035 (light gray)

Environmental data	
Operation temperature	-40 °C ... 70 °C
Storage temperature	-40 °C ... 70 °C
Environment (application)	Indoor/Outdoor
Ingress protection (IP Rating)	IP66
Flammability rating	UL 94-V0

Ordering information		
Item description	Item number	Product name
1399.17.0272	85178889	SENCITY® Urban 200

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35382 / Date of publication: 14.08.2025 / uncontrolled copy