

SENCITY® Road MULTI Antenna

1399.99.0410

Properties

- Rugged vehicle rooftop multi-band antenna for commercial vehicles like bus and truck
- Supports 2G/3G/4G/5G cellular, Wifi 2.4/5 GHz, Wifi 6E and GNSS (Beidou, Galileo, GPS, Glonass)
- 7 separate ports for 4x4 cellular MIMO and 2x2 Wifi MIMO plus GNSS
- Single hole mounting, easy cabling feed-through
- Meets ISO16750 automotive standard
- Fire retardant acc. to ECE-R118



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	Cellular 1-4	Cellular 1-4	Cellular 1-4	Cellular 1-4
Frequency	617 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz	4900 MHz ... 7125 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2.1	2	2
Gain	2 dBi	4 dBi	4 dBi	5 dBi
Isolation between Ports	9 dB	18 dB	15 dB	18 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7
Name	WiFi 1-2	WiFi 1-2	GNSS
Frequency	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz	1559 MHz ... 1610 MHz
Impedance	50 Ω	50 Ω	50 Ω
VSWR	2	2	1.8
Gain	6 dBi	6 dBi	
Isolation between Ports	24 dB	24 dB	
Ambient Temperature	25 °C	25 °C	

SENCITY® Road MULTI Antenna

1399.99.0410

	Band 5	Band 6	Band 7
Composite Power max	30 W	30 W	

Electrical remarks

Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.
---------	--

Ports

	Port 1 to 4	Port 5 to 6	Port 7
Port name	Cell 1-4 (White)	WiFi 1-2 (blue)	GNSS (black)
Connector	SMA, plug (male)	SMA, plug (male)	TNC, plug (male)
Cable type	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM
Cable length	0.3 m	0.3 m	0.3 m
Polarization	vertical	vertical	circular right
DC grounded	Yes	Yes	No

Connections

	Port 1 to 4	Port 5 to 6	Port 7
Port name	Cell 1-4 (White)	WiFi 1-2 (blue)	GNSS (black)
Band 1	✓		
Band 2	✓		
Band 3	✓		
Band 4	✓		
Band 5		✓	
Band 6		✓	
Band 7			✓

Electrical data LNA

LNA is connected to	Port 5
Input voltage	3 V ... 5 V
Current consumption	20 mA
Noise figure	1.6 dB
Total gain @90° elevation	30 dBic

Mechanical data

Weight	1.1 kg
Dimensions	60 mm x 210 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data

Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminium

SENCITY® Road MULTI Antenna

1399.99.0410

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP68, IP69k
Flammability rating	ECE-R118
Solar radiation	DIN 75220

Environmental remarks

Environmental tests: ISO 16750:2012/2010
 Low corrosion designed acc. to MIL-F-14072D
 ECE-R10
 E-Mark
 CE-Mark

Ordering information

Item description	Item number	Product name
1399.99.0410	85192478	SENCITY® Road MULTI Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
 DOCUMENT PIM-P35227 / Date of publication: 04.06.2025 / uncontrolled copy