

COAXIAL CONNECTOR, MMBX, 50 Ohm, Right angle cable plug (male)

16_MMBX-50-2-2/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection



Product configuration

Interface type	Gender	Standard
MMBX	plug	HUBER+SUHNER-MMBX

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data

Weight	0.0011 kg
Mating cycles	100
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min		8 N
Interface force max	30 N	30 N

COAXIAL CONNECTOR, MMBX, 50 Ohm, Right angle cable plug (male)

16_MMBX-50-2-2/111_N

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23001746	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
84028931	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23001746	16_MMBX-50-2-2/111_NE	Single
84028931	16_MMBX-50-2-2/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	U4 - 2 mm / 50 Ohm
Suitable cables	K_02252_D
	G_02232_D
	ENVIROFLEX_316_D

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies
22543139	74_Z-0-0-30	Assembly tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3120 / Date of publication: 12.07.2025 / uncontrolled copy