

COAXIAL CONNECTOR, QLA-01, 50 Ohm, Right angle cable plug (male)

16_QLA-01-2-13/122_N

Properties

- The coupling mechanism provides a fast and reliable connection
- Intermateable with Lemo series 00.250
- Applicable in frequencies up to 1.4 GHz



Product configuration		
Interface type	Gender	Standard
QLA-01	plug	NIM-CAMAC-Standard CD/N549
Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	50 Ω	
Interface frequency	1.4 GHz	
Mechanical data		
Weight	0.0046 kg	
Mating cycles	10000	
Cable entry centre contact	soldered	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-55 °C ... 150 °C	

COAXIAL CONNECTOR, QLA-01, 50 Ohm, Right angle cable plug (male)

16_QLA-01-2-13/122_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22544279	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22544279	16_QLA-01-2-13/122_NE	Single

Suitable cables	
Cable group	U3 - 2 mm / 50 Ohm
Suitable cables	G_01130_HT

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3065 / Date of publication: 11.07.2025 / uncontrolled copy