

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable jack (female)
21_N-50-4-76/133_U

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Gender	Standard	
jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210	
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	50 Ω	
Interface frequency	11 GHz	
Mechanical data		
Weight	0.0356 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-65 °C ... 165 °C	

COAXIAL CONNECTOR, N, 50 Ohm, Straight cable jack (female)

21_N-50-4-76/133_U

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22658836	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22658836	21_N-50-4-76/133_UH	Bulk 100 pcs

Suitable cables	
Cable group	X9 - 4 mm / 50 Ohm
	S16 - 4 mm / 50 Ohm

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543189	76_Z-0-4-1	Crimping dies
22543185	76_Z-0-3-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2881 / Date of publication: 11.07.2025 / uncontrolled copy