

COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_N-50-0-3/133_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration

Interface type	Gender	Standard
N	jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	Glass Bead	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data

Weight	0.0465 kg
Mating cycles	500
Flange type	round flange / dia. 21
Tab style	Special

Environmental data

Operation temperature	-50 °C ... 160 °C
-----------------------	-------------------

COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_N-50-0-3/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22644425	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22644425	22_N-50-0-3/133_NE	Single

Additional Information	
Remarks	Hermetically sealed: leak rate $\leq 10^{-6}$ Torr l/s (atm cc/s)

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2795 / Date of publication: 12.07.2025 / uncontrolled copy