


COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_SMA-50-0-41/133_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz



Product configuration

Interface type	Gender	Standard
SMA	jack	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0023 kg
Mating cycles	500
Flange type	2-hole flange / 16 X 5.7
Tab style	solder end

Environmental data

Operation temperature	-65 °C ... 125 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_SMA-50-0-41/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543984	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22644383	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543984	23_SMA-50-0-41/133_NE	Single
22644383	23_SMA-50-0-41/133_NH	Bulk 100 pcs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2700 / Date of publication: 12.07.2025 / uncontrolled copy