


COAXIAL CONNECTOR, MCX, 50 Ohm, Straight bulkhead cable jack (female)

24_MCX-50-2-7/111_N

Properties

- Small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration

Interface type	Gender	Standard
MCX	jack	IEC 60169-36_CEEC 22220

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data

Weight	0.0014 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min		8 N

COAXIAL CONNECTOR, MCX, 50 Ohm, Straight bulkhead cable jack (female)

24_MCX-50-2-7/111_N

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force max	25 N	20 N

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23000468	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23000468	24_MCX-50-2-7/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	U2 - 2 mm / 50 Ohm
Suitable cables	RG_316_/U
	RG_188_A/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543181	76_Z-0-2-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2637 / Date of publication: 11.07.2025 / uncontrolled copy