


COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead cable jack (female)

24_N-50-4-53/133_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration	
Gender	Standard
jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0385 kg
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 125 °C

COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead cable jack (female)

24_N-50-4-53/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22644946	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22644946	24_N-50-4-53/133_NE	Single

Suitable cables	
Cable group	X9 - 4 mm / 50 Ohm S16 - 4 mm / 50 Ohm
Suitable cables	S_04272_B

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22646290	74_Z-0-0-264	Trimming tool
23036529	76_Z-0-4-18	Crimping dies
84072013	74_Z-0-0-472	Assembly tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2612 / Date of publication: 11.07.2025 / uncontrolled copy