

COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead cable jack (female)

24_N-50-7-24/133_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration

Gender	Standard
jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data

Weight	0.0393 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, N, 50 Ohm, Straight bulkhead cable jack (female)

24_N-50-7-24/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22649912	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22649912	24_N-50-7-24/133_NE	Single

Suitable cables	
Cable group	U33 - 7 mm / 50 Ohm
Suitable cables	RG_393_/U
	ENVIROFLEX_393

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22642718	74_Z-0-0-12	Knives / Blades

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2608 / Date of publication: 11.07.2025 / uncontrolled copy