

COAXIAL CONNECTOR, TNC-reverse, 50 Ohm, Straight bulkhead cable jack (female)

24_TNC-R50-4-60/133_N

Properties

- Threaded coupling mechanism improves control over the interface dimensions
- Used under a higher environmental load than BNC
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 11 GHz



Product configuration		
Interface type	Gender	Standard
TNC-reverse	jack	HUBER+SUHNER-TNC-R50 (reverse polarity)

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0.1 GHz ... 2 GHz	33 dB	1.046
2 GHz ... 4 GHz	31 dB	1.058
4 GHz ... 6 GHz	26 dB	1.106

COAXIAL CONNECTOR, TNC-reverse, 50 Ohm, Straight bulkhead cable jack (female)

24_TNC-R50-4-60/133_N

Mechanical data	
Weight	0.0181 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84032154	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84032154	24_TNC-R50-4-60/133_NE	Single

Suitable cables	
Cable group	X34 - 4 mm / 50 Ohm X28 - 4 mm / 50 Ohm
Suitable cables	SPUMA_240-RS-FR SPUMA_240

Additional Information	
Remarks	Reverse polarised interface
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544758	76_Z-0-4-51	Crimping dies
22543189	76_Z-0-4-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2529 / Date of publication: 11.07.2025 / uncontrolled copy