

COAXIAL ADAPTER, UHF, X Ohm, jack / jack (female / female)

31_UHF-0-0-1/022_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
UHF	jack (female)	IEC 60169-12
UHF	jack (female)	IEC 60169-12

Interface and material data

UHF		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PP (Polypropylene)	
UHF		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PP (Polypropylene)	

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0202 kg
Mating cycles	500

Environmental data

Operation temperature	-25 °C ... 100 °C
-----------------------	-------------------

COAXIAL ADAPTER, UHF, X Ohm, jack / jack (female / female)
31_UHF-0-0-1/022_-

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22542810	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22542810	31_UHF-0-0-1/022_-E		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2358 / Date of publication: 12.07.2025 / uncontrolled copy