


32085E-29447P-29094CR-12, VITA 67.3 NanoRF (male), SMA (male), 50 Ohm, 26.5 GHz, 12 in, 304.8 mm

32085E-29447P-29094CR-12

Properties

- Assembly with VITA 67.3 compliant NanoRF connector
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 047 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Applicable up to 26.5 GHz
- Low loss PTFE dielectric



Product configuration	
Configuration type	One pair of assemblies
Type of cable	MICROBEND L (32085E)
Type description connector A	29447P-32-85
Series connector A	NanoRF, straight - plug
Type description connector B	29094CR-32-85
Series connector B	SMA, straight - plug
Length	304.8 mm
Length	12 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	26.5 GHz
VSWR max	1.5
Max. insertion loss	1.77 dB
Propagation velocity	76 %

Electrical Data (frequency related)			
Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	21.66 dB	1.18	0.47 dB
2 GHz ... 12 GHz	16.53 dB	1.35	1.16 dB
12 GHz ... 18 GHz	15.56 dB	1.4	1.42 dB
18 GHz ... 26.5 GHz	13.97 dB	1.5	1.77 dB

32085E-29447P-29094CR-12, VITA 67.3 NanoRF (male), SMA (male), 50 Ohm, 26.5 GHz, 12 in, 304.8 mm
32085E-29447P-29094CR-12

Mechanical data	
Weight	8 g
Cable diameter	1.96 mm
Static bending radius	5.08 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
85259496	32085E-29447P-29094CR-12

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P58476 / Date of publication: 10.06.2025 / uncontrolled copy