

PLUG: WTB 20-6 PR9 SC
 RECEPTACLE: WTB 20-6 SAC SC
 XXX XXXX XXX XX

PLUG

RECEPTACLE

SERIES			
WTB	Plug, right angle, with mounting ears	WTB	Receptacle, straight, with mounting ears
SIZE			
20-6	20 right angle signal pins, plus 6 straight or right angle removable coax sockets	20-6	20 straight signal pins, plus 6 straight removable coax pins
CONTACTS			
TYPE CONTACTS/TERMINATIONS:		TYPE CONTACTS/TERMINATIONS:	
PR7	Pin, right angle, dip solder, .109" x .025" dia	SAC	Socket, straight, solder cup (.035" I.D.)
PR9	Pin, right angle, dip solder, .140" x .025" dia	SAD9	Socket, straight, dip solder, .140" x .027" dia
PR11	Pin, right angle, dip solder, .172" x .025" dia	SAD11	Socket, straight, dip solder, .172" x .027" dia
		SAD15	Socket, straight, dip solder, .234" x .027" dia
		SAG7	Socket, straight, dip solder, .109" x .018" dia
		SAG9	Socket, straight, dip solder, .140" x .018" dia
		SAG11	Socket, straight, dip solder, .172" x .018" dia
HARDWARE			
SC	Guide set	SC	Guide set
SC-#	Guide set, polarized	SC-#	Guide set, polarized

OPTIONS	
<ul style="list-style-type: none"> Molded insulator: Diallyl Phthalate per ASTM-D5948 (GDI-30F or SDG-F) Removable type coax contacts sold separately. See "Coax Contacts" in Accessories section for instructions. Coax Contacts: <ul style="list-style-type: none"> WTC188P = straight pin (to be installed in receptacle insulator only) WTC196P = straight pin (to be installed in receptacle insulator only) WTC085P = straight pin (to be installed in receptacle insulator only) WTC188S = straight socket (to be installed in plug insulator only) WTC196S = straight socket (to be installed in plug insulator only) WTC085S = straight socket (to be installed in plug insulator only) WTC10SRD9 = right angle socket (to be installed in plug insulator only) Option Codes: Add to the end of the part number. Example: WTB20-6SAD9SC342. Call factory for additional codes. 	
-342	Remove mounting ears. (.250" each end)
-C34	Remove .225" standoff so connector is flush to board (receptacle only).
-G69	Solder cups are fixed in an outward orientation, otherwise contacts can rotate.
-D01	Pretinned contact terminations (except solder cups, wire wraps [®] and flex contacts) with 63/37 or 60/40 solder. ☒
-P39	Pretinned contact terminations (except solder cups, wire wraps [®] and flex contacts) with SAC305 solder (lead free).
☒ = Option not RoHS compliant	