

COAXIAL ADAPTER, TNC, 50 Ohm, plug / plug (male / male)

32_TNC-50-0-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
TNC	plug (male)	IEC 60169-17_MIL-STD-348A/313_CECC 22200
TNC	plug (male)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
TNC		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
TNC		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz
VSWR	DC - 11 GHz ($\leq 1.03 + 0.05 f \text{ GHz}$)

COAXIAL ADAPTER, TNC, 50 Ohm, plug / plug (male / male)

32_TNC-50-0-1/133_N

Mechanical data	
Weight	0.0278 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543407	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543407	32_TNC-50-0-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2277 / Date of publication: 12.07.2025 / uncontrolled copy