

COAXIAL ADAPTER, SMA, 50 Ohm, plug / jack (male / female)

33_SMA-50-0-51/199_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CECC 22110
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PFA / PTFE	
Coupling nut	Stainless steel	
Gasket	VMQ (Silicone rubber)	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz
VSWR	DC - 18 GHz ($\leq 1.05 + 0.008 f \text{ GHz}$)

COAXIAL ADAPTER, SMA, 50 Ohm, plug / jack (male / female)

33_SMA-50-0-51/199_N

Mechanical data	
Weight	0.0051 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22644253	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22644253	33_SMA-50-0-51/199_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2163 / Date of publication: 12.07.2025 / uncontrolled copy