

#### NOTES:

- 1. ALLOWABLE FLEXIBLE LIGHT PIPE CUT LENGTH AVAILABLE IN INCREMENTS OF 0.05".
- 2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 0.87" [22mm].
- 3. COMPONENTS SHIPPED NON-ASSEMBLED.
- 4. SEE SHEET 2 FOR DETAILED ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET


REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED		
Α	A Engineering Release		A.V.		







## PART NUMBER CONFIGURATOR

SEE SHEET 2 FOR ORDERING INFORMATION



### RECOMMENDED LENS MOUNTING HOLE





## **CUSTOMER USE DRAWING**

STANDARD TO (UNLESS OTHERWIS DECIMALS .X ± .1 .XX ± .02		4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974			
.XXX ± .010	⊕ ⊡	TITLE: FLP ASSEMBLY WITH LOW PROFILE ADAPTER, LC			
DESIGNED: K. BARON	3/1/2022	DRAWING NO:  SZR1-X.XX-F4PX-X  REVISION A			REVISION:
REVISED: N/A	DATE: N/A	SHEET A		<b>CAGE CODE</b> : 32559	
CHECKED: DATE: 3/1/2022		SCALE: 2	2:1	SHEET # 1	<b>OF</b> 2
		CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			


TABLE 1 - LENGTH			
LENGTH (L)* TOLERANCE			
1.00" - 16.00"	±0.05"		
16.05" - 40.00"	±0.15"		
40.05" - 80.00"	±0.30"		
80.05" - 3,940.00"	±0.5%		

4 4 3 / 4 11	4 D. E IV	0 0 5 11	ILLODE	4ENITO
^AVAII	ABI F IN	0.05"	INCREI	/IFN IS

TABLE 2 - LENS			
ORDER CODE	LENS APPEARANCE		
(BLANK)	CLEAR		
D	DIFFUSED		
S	SMOKED		
BE	TINTED BLUE		
GN	TINTED GREEN		
RD	TINTED RED		
YW	TINTED YELLOW		

TABLE 3 - CABLE			
CABLE COLOR			
BLACK			
RED			
YELLOW			
GREEN			
BLUE			
WHITE			

## **SAMPLE PART NUMBER:**



### **ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET:**

- CLEAN PANEL SURFACE AROUND MOUNTING HOLE WITH ALCOHOL
- PEEL LINER OFF TOP OF THE SEALING GASKET WHILE KEEPING SEALING GASKET ON PLASTIC ROLL
- APPLY SEALING GASKET TO PANEL HOLE AS CENTERED AS POSSIBLE AND PEEL PLASTIC LINER SLOWLY AWAY
- INSERT LIGHT PIPE INTO PANEL UNTIL SEALING GASKET MATERIAL IS COMPRESSED BETWEEN LENS AND PANEL
- HOLD FOR A FEW SECONDS TO ENSURE ENTIRE SEALING GASKET ADHERES TO PANEL AND LENS FLANGE SURFACE

# **CUSTOMER USE DRAWING**

	BIVAR®				
CAGE CODE:	32559	DRAWING NO: SZR1-X.XX-F4PX-X			REVISION:
SHEET SIZE:	Α	SCALE: CAD GEN	2:1 ERATED DOCUMEN	SHEET # 2 OF 2 ED DOCUMENT, DO NOT MEASURE DRAWIN	