

COAXIAL FIXED ATTENUATOR, 50 Ohm, 6 dB, SMA

5906_SMA-50-010/19-_N

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.

**Product configuration**

Interface	Gender	Standard
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CEECC 22110
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CEECC 22110

Electrical data

Impedance	50Ω
Operating frequency	0 GHz ... 18 GHz
Attenuation nominal	6 dB
VSWR	1.35
Return loss	16.5 dB

Electrical Data (frequency related)

Frequency range	Attenuation deviation	VSWR max
0 GHz to 18 GHz	+/- 0.6 dB	1.35

Electrical Data (power)

Average power	10 W at 25 °C ambient temperature. Linearly derated to 1 W at 100 °C ambient temperature.
Peak power	500 W, 5 μs pulse width, 1 % duty cycle

Interface and material data

Interface	SMA / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Stainless steel	Passivated (Plating)
Body	Aluminium	Anodized
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless steel	Passivated (Plating)

COAXIAL FIXED ATTENUATOR, 50 Ohm, 6 dB, SMA

5906_SMA-50-010/19-_N

Interface and material data		
Interface	SMA / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Stainless steel	Passivated (Plating)
Body	Aluminium	Anodized
Insulator	PTFE (Polytetrafluoroethylene)	

Mechanical data	
Weight	0.016 kg

Environmental data	
Operation temperature	-55 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85177191	RoHS 2011/65/EU and (EU) 2015/863	Compliant without exemption	
	REACH 1907/2006 Article 33 SVHC	Free of SVHC >0,1%	

Ordering Information Table	
Item number	Item description
85177191	5906_SMA-50-010/19-_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1842 / Date of publication: 08.08.2025 / uncontrolled copy