

COAXIAL TERMINATION, 50 Ohm, 7/16, plug (male)

6525.41.AB

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power

**Product configuration**

Interface	Gender	Standard
7/16	plug (male)	IEC 60169-4_CECC 22190_DIN 47223_VG 95250

Electrical data

Impedance	50Ω
Operating frequency	0 GHz ... 2 GHz
VSWR	1.1
Return loss	26.4 dB

Electrical Data (frequency related)

Frequency range	VSWR max	Return loss
0 GHz to 2 GHz	1.1	

Electrical Data (power)

Average power	25 W at 25 °C ambient temperature. Linearly derated to W at 150 °C ambient temperature.
Peak power	1500 W, 5 μs pulse width, 0.05 % duty cycle

Interface and material data

Interface	7/16 / plug (male)	
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Aluminium	Anodized
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

COAXIAL TERMINATION, 50 Ohm, 7/16, plug (male)
6525.41.AB

Interface and material data		
Gasket	VMQ (Silicone rubber)	
Piece parts	Material	Plating
Mechanical data		
Weight	0.204 kg	
Environmental data		
Operation temperature	-40 °C ... 150°C	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1712 / Date of publication: 09.11.2023 / uncontrolled copy