

Specification Sheet

Part Number: T50LDH9M4

The tie contains a dual locking design to secure two bundles at once.

Head design can also provide spacing between parallel bundles.

Bent tail allows for quick insertion into head.



Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66, Natural, 1000/pkg

Article Number	117-05461
----------------	-----------

Type	T50LDH
------	--------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	--

Short Description	Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66, Natural, 1000/pkg
-------------------	---

Global Part Name	T50LDH-PA66-NA
------------------	----------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	15.60
---------------------	-------

Length L (Metric)	395.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	3.94
--------------------------------	------

Bundle Diameter Max (Metric)	100
------------------------------	-----

Bundle Diameter 1st Loop Max (Imperial)	4.0
---	-----

Bundle Diameter 1st Loop Max (Metric) 101.6

Bundle Diameter 2nd Loop Max (Imperial) 2.0

Bundle Diameter 2nd Loop Max (Metric) 50.8

Thickness T (Metric) 1.4

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Certification/Specification UL | ANSI/UL 746B UL | ANSI/UL 62275 UL | ANSI/UL 1565

UL Recognized (US) Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)