

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, PC 2.4

6610_PC24-50-1/199_N

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.



Product configuration		
Interface	Gender	Standard
PC 2.4	plug (male)	
PC 2.4	jack (female)	

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 50 GHz
Attenuation nominal	10 dB
VSWR	1.3
Return loss	17.7 dB

Electrical Data (frequency related)		
Frequency range	Attenuation deviation	VSWR max
0 GHz to 50 GHz	+/- 0.8 dB	1.3

Electrical Data (power)	
Average power	2 W at 25 °C ambient temperature. Linearly derated to 0.3 W at 100 °C ambient temperature.
Peak power	100 W, 5 μs pulse width, 1 % duty cycle

Interface and material data		
Interface	PC 2.4 / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PEI (Polyether-imide)	
Coupling nut	Stainless Steel	Passivated (Plating)

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, PC 2.4
6610_PC24-50-1/199_N

Interface and material data		
Gasket	VMQ (Silicone rubber)	
Interface	PC 2.4 / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PEI (Polyether-imide)	

Mechanical data	
Weight	0.004 kg

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering Information Table	
Item number	Item description
85177164	6610_PC24-50-1/199_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1668 / Date of publication: 21.11.2024 / uncontrolled copy