

Specification Sheet

Part Number: 151-01113

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.



An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip, with Edge Clip, 1.4" Long, PA66HIRHS, Black, 5000/box

Article Number	151-01113
----------------	-----------

Type	EC46
------	------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip, with Edge Clip, 1.4" Long, PA66HIRHS, Black, 5000/box
-------------------	---

Global Part Name	EC46-PA66HIRHSUV-BK
Length L (Imperial)	1.4
Length L (Metric)	35.5
Fixation Method	Edge Clip
Variant	1.0 - 3.0 mm Edge
Width W (Imperial)	0.44
Width W (Metric)	11.18
Height H (Imperial)	0.56
Height H (Metric)	14.15
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)