

Specification Sheet

Part Number: 156-02087



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 12 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Article Number 156-02087

Type MOC12FMOC16M180

Color Black (BK)

Quantity Per pack

Product Description The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Short Description MOC Clip to MOC Clip Perpendicular, 12 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Global Part Name MOC12FMOC16M180-PA66HIRHSUV-BK

Length L (Imperial)	1.92
Length L (Metric)	48.77
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.41
Bundle Diameter Min (Metric)	10.5
Bundle Diameter Max (Imperial)	0.54
Bundle Diameter Max (Metric)	13.8
Height H (Imperial)	0.90
Height H (Metric)	22.9
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)